

## 1994 54" Refrigeration Valves and Systems Corporation (RVS) Ammonia Recirculator

Mfg: RVS

Model: RSK2779

Stock No. ASAC009.

Serial No. 93718

1994 54" Refrigeration Valves and Systems Corporation (RVS) Ammonia Recirculator - 54"x 12'7", 1000 Gallon. Model: RSK2779. S/N: 93718. Nat'l Bd: 6423. Capacity: 750 TR @ +22 °F. MAWP: 250 psi @ 300 °F. MDMT: -20 °F @ 250 psi. 2003 Hansen Technologies Hermetic Centrifugal Pump, Model: CNF 50-160/1, S/N: 411000 1128/11-01, capacity: 29-220 gpm (6.5-50 cu. m/hr), impeller diameter: 6.22 in. AGX Motor, 13.5 hp (10.2 kW), 3380 rpm, 440 V, 16 amps, 60 Hz, 3 phase. 1993 Hansen Technologies Hermetic Centrifugal Pump, Model: CNF 50-160, S/N: CH65423, capacity: 29-220 gpm (6.5-50 cu. m/hr), impeller diameter: 6.22 in. AGX Motor, 10 hp (7.4 kW), 3380 rpm, 440 V, 16 amps, 60 Hz, 3 phase. Refrigeration Valves and Systems Corp. Oil Tank, S/N: 93803, Nat'l Bd: 6142, MAWP: 300 psi @ 300 °F, MDMT: -20 °F @ 300 psi. Hansen Technologies Ammonia Vari-Level LB5 Control Panel. Inlets: (2) 1-1/2 in. dia. ports, (1) 3 in. dia. port, (2) 8 in. dia. ports. Outlets: (1) 3/4 in. dia. FNPT (oil drain valve), (1) 3/4 in. dia. FNPT. Vessel dimensions: 54 in. diameter x 12 ft. 7 in. L. Overall dimensions: 13 ft. 8 in. L x 92 in. W x 12 ft. H.





