

66 in. RVS Recirculator Package

Mfg: RVS

Model:

Stock No. ASLC005.

Serial No. 94804

1995 60 in. RVS Recirculator Package. Insulated Ammonia Recirculator Tank- 2500 Gallon. S/N: 94804. Nat'l Bd: 7956. Surface area: 278 sq. ft. MAWP: 250 psi @ 300°F. MDMT: -20°F @ 250 psi. Head thickness: 5/8 in. Shell thickness: 5/8 in. (2) 1995 Cornell Centrifugal Pumps, Model: 1.5SCBH-7.5-4, S/Ns: 91233,91234, impeller diameter: 12.38 in., capacity: 90 gpm, 165 psid. (2) Baldor Industrial Motors, 5 and 7-1/2 hp, 1740 and 1760 rpm, 190/360-230/460 V, 16/8 and 19.6/9.8 amps, 50/60 Hz, 3 phase. RVS Tank-12 Gallon, surface area: 9 sq. ft., head and shell thickness: 0.365 in. 2002 Shank Relief Valve, Type 803, 250 PSIG set Pressure, 1/2 in. purge outlet. Inlets: (1) 10 in. port, (1) 1-1/2 in inlet port. Outlets: (1) 8 in. outlet port, (1) 3 in. outlet port, (1) 1-1/2 in. outlet port. Overall dimensions: 108 in. L x 99 in. W x 20 ft. 8 in. H. (ACN460).





