

60" RVS Recirculator Package

Mfg: RVS

Model:

Stock No. ASLC007.

Serial No. 94802

1995 60" RVS Recirculator Package. Insulated Ammonia Recirculator Tank- 1650 Gallon. S/N: 94802. Nat'l Bd: 7979. Surface area: 230 sq. ft. MAWP: 250 psi @ 300°F. MDMT: -30°F @ 100 psi. Head thickness: 5/8 in. Shell thickness: 5/8 in. (2) 1995 Cornell Centrifugal Pumps, Model: 2CB-5-4, S/Ns: 91233, 91232, impeller diameter: 10.38 in., capacity: 102 gpm, 108 psid. (2) Baldor Industrial Motors, 3 hp, 1470 and 1760 rpm, 190/380-230/460 V, 11/5.5 and 13.6/6.8 amps, 50/60 Hz, 3 phase. RVS Tank-12 Gallon, head and shell thickness: 0.365 in. (2) Cyrus Shank Pressure Relief Valves, Type 803, 250 psig set pressure, air capacity: 573 cfm, 1/2 in. purge outlet. Inlets: (1) 10 in. port, (1) 1-1/2 in inlet port. Outlets: (1) 8 in. outlet port, (1) 3 in. outlet port, (1) 1-1/2 in. outlet port. Overall dimensions: 108 in. L x 99 in. W x 20 ft. 8 in. H.





