

Jones Beloit Corp. Pressmaster Vertical Juice Press

Mfg: Jones Beloit

Model: P-125

Stock No: CCFP134

Serial No: P-497

Jones Beloit Corp. Pressmaster Vertical Juice Press. Model P-125. S/N: P-497. Hopper inlet tank on top with fill probes. Product press dimensions: 1 ft. 9 in. dia. x 3 ft. 11 in. H. US electric Varidrive motor, 10 hp, 1725 rpm, 208-220 V, 30-28 amps, 60 Hz, 3 phase. Minimum rpm: 450. Maximum rpm: 3600. Approximate weight: 7,100 lbs. Inlets: (1) 1 ft. 6 in. Open top (hopper). Outlets: (1) 6-1/2 in dia. S-line fitting (juice out). (1) 1 ft. 2 in. W x 5-1/2 in. H. pulp trough. Overall dimensions: 9 ft. 7 in. L x 5 ft. 7 in. W x 14 ft. 1 in. H.











