

6 Head Rotary Filler Model AG62

Mfg:

Model: AG62

Stock No: CCFP500

Serial No:

6-Head Rotary Filler. Model: AG62. (6) 1-1/4 in. dia. nozzles will fill 8-1/2 in. H (max) bottle. Distance between valves: 10 in. Conveyor: 3-1/2 in. W x 48 in. L. Infeed height: 33 in. (adjustable). Exit height: 32 in. (adjustable). Infeed Tank- 19 gal., inside dimensions: 24 in. dia. x 10 in. H. Unit features a tamping foot for press-on caps, less chute. Baldor Industrial Motor, 1/2 hp, 208-230/460 V, 3.4-3.2/1.6 amps, 60 Hz, 3 phase. Overall dimensions: 55 in. L x 44 in. W x 56 in. H.



