

SPECIFICATIONS (BARE COMPRESSOR)

Item	Single-stage compressor									Compound compressor					
	2WA	4WA(J)	6WA(J)	8WA(J)	4WB	6WB	8WB	12WB	42WA	62WA	42WB	62WB	12.4WB		
Refrigerant	R717, R22, R502, R12, Propane														
Type	Reciprocating, open type														
No. of cylinders	2	4	6	8	4	6	8	12	L-4/H-2	L-6/H-2	L-4/H-2	L-6/H-2	L-12/H-4		
Bore	3-3/4 (95)			5-1/8 (130)				3-3/4 (95)		5-1/8 (130)					
Stroke	3 (76)			3-15/16 (100)				3 (76)		3-15/16 (100)					
Max. speed	1,100			1,450				1,200		1,450		1,200			
Displacement at max. speed	CFM (m ³ /h)	42 (71)	110 (187)	165 (281)	220 (374)	224 (381)	337 (573)	450 (764)	674 (1,145)	L-110 (187)	L-165 (281)	L-224 (381)	L-337 (573)	L-674 (1,145)	
										H-55 (94)	H-55 (94)	H-112 (191)	H-112 (191)	H-224 (381)	
Driving method*	Belt drive or direct drive														
Capacity control steps	%	100	100, 50	100, 66, 33	100, 75, 50, 25	100, 50	100, 66, 33	100, 75, 50, 25	100, 66, 33	100, 50	100, 66, 33	100, 50	100, 66, 33	100, 66, 33	
Refrigeration oil	ISO VG68 or equivalent														
Oil charge quantity	U.S. gal. (l)	1.32 (5)	3.17 (12)	3.70 (14)	4.49 (17)	5.29 (20)	6.61 (25)	6.87 (26)	13.74 (52)	3.70 (14)	4.49 (17)	6.61 (25)	7.00 (26.5)	14.53 (55)	
Connections	Suction	R717	2" (50A)	2-1/2" (65A)	3" (80A)	3-1/2" (90A)	3-1/2" (90A)	4" (100A)	5" (125A)	L2" (50A)	L2-1/2" (65A)	L3" (80A)	L4" (100A)	L5" (125A)	
		R22, R502	2-1/2" (65A)	3" (80A)	3-1/2" (90A)		4" (100A)	5" (125A)		H-1 1/2" (40A)	H-1 1/2" (40A)	H-2 1/2" (65A)	H-2 1/2" (65A)	H-3" (80A)	H-3" (80A)
	Discharge	R717	2" (50A)	2-1/2" (65A)	3" (80A)	3" (80A)	3-1/2" (90A)	3" (80A)	3-1/2" (90A)	3" (80A) x 2	L2" (50A)	L2" (50A)	L2-1/2" (65A)	L2-1/2" (65A)	L3" (80A) x 2
		R22, R502	2" (50A)	2-1/2" (65A)	3" (80A)	3-1/2" (90A)	4" (100A)	3-1/2" (90A)	4" (100A)	H-1 1/2" (40A)	H-1 1/2" (40A)	H-2" (50A)	H-2" (50A)	H-2" (50A) x 2	H-2" (50A) x 2
Net weight	lb. (kg)	810 (370)	(A) 1,280 (580) (J) 1,100 (500)	(A) 1,540 (700) (J) 1,230 (560)	(A) 1,800 (820) (J) 1,430 (650)	2,420 (1,100)	3,100 (1,410)	3,410 (1,150)	5,500 (2,500)	1,580 (720)	1,850 (840)	3,170 (1,440)	3,430 (1,560)	6,820 (3,100)	

Note: "L" - Low stage, "H" - High stage. * Model 12.4WB - Direct drive only.

ITEMS INCLUDED

- Suction shut-off valve 1 pc. (Single-stage), 2 pcs. (Compound)
- Discharge shut-off valve 1 pc. (Single-stage), 2 pcs. (Compound)
- Oil cooler 1 pc.
- Flywheel 1 pc.
- Safety valve 1 pc. (Single-stage), 2 pcs. (Compound)
- Capacity control solenoid valve* 1 pc.**
- * Excludes compressors for chemical plants. ** Excludes Model 2WA.
- Discharge side thermometer 1 pc. (Single-stage), 2 pcs. (Compound)
- Suction side thermometer 1 pc. (Single-stage), 2 pcs. (Compound)
- Service tools 1 set

PRIMARY CHOICES



- Driving method (Belt drive, Direct drive)
- Control panel (Mechanical type, Microprocessor type)
- Head cover (Air-cooled, Water-cooled, DX-cooling)
- Oil cooler (Water-cooled, DX-cooling)
- Oil filter (Cuno-filter, External filter, Both)
- Gasket (Non-asbestos, Asbestos)

OPTIONAL ACCESSORIES

- High pressure cut-out switch
- Low pressure cut-out switch
- Oil pressure failure protection switch
- High pressure side pressure gauge
- Low pressure side pressure gauge
- Oil pressure gauge
- Gauge board
- Oil heater with thermo-switch
- Oil separator
- Capacity control solenoid valve

OUTER DIMENSIONS (COMPRESSOR UNIT)

Unit: in. (mm)



Model	Dimensions									Flywheel		Weight less motor lb. (kg)	
	A	B	C	D		E	F	G	L*	W	Pitch dia.		No. of grooves
2WA	12-5/8(321)	-	37-1/2(955)	17(432)	-	21(533)	-	-	58(1,475)	34(865)	13-1/4(336)	C x 4	975(442)
4WA	17-3/4(451)	12-1/16(306)	45-7/8(1,165)	15(381)	11(279)	25(635)	66-1/2(1,680)	38(965)	67(1,705)	42(1,070)	15-7/16(392)	C x 4	2,005(909)
6WA	17-3/4(451)	32-1/16(814)	47-7/8(1,220)	4(102)	4(102)	25(635)	73-3/4(1,875)	41(1,045)	69-1/2(1,765)	43-1/2(1,105)	15-7/16(392)	C x 6	2,280(1,034)
8WA	18-15/16(481)	32-7/16(824)	50-1/16(1,290)	4-1/2(114)	4-1/2(114)	25(635)	78(1,985)	41-1/2(1,055)	71(1,805)	44-1/8(1,125)	15-7/16(392)	C x 8	2,605(1,181)
4WB	20-1/2(521)	15-13/16(402)	55-1/2(1,410)	20(508)	12-1/2(318)	27(686)	82(2,085)	44-1/2(1,130)	81(2,060)	55(1,400)	17-9/16(446)	C x 8	3,430(1,556)
6WB	21-5/16(541)	40-3/8(1,026)	58-5/16(1,485)	5(127)	5(127)	28(711)	92(2,340)	50(1,270)	82-3/4(2,105)	55(1,400)	17-9/16(446)	C x 10	3,980(1,805)
8WB	21-1/4(540)	39-11/16(1,008)	60-13/16(1,545)	6-1/2(165)	5-1/2(140)	30(762)	95(2,415)	48-1/2(1,235)	83-3/4(2,130)	55-1/4(1,405)	17-9/16(446)	C x 10, C x 12	4,420(2,005)
12WB	B.D.	23-1/4(591)	61-1/2(1,565)	5(127)	5(127)	72(1,829)	122-1/4(3,120)	53-3/16(1,355)	88(2,235)	79(2,010)	17-9/16(446)	C x 12	7,740(3,510)
	D.D.	25-1/4(641)	63-1/2(1,613)								63-1/2(1,615)	-	-

Note: "B.D." - Belt drive. "D.D." - Direct drive.
 * Dimension L given is less motor. Motor junction box may extend beyond frame especially on larger motor sizes.
 * Figure in bracket []: Compressors for Canada only.

Design and specifications subject to change without notice.

For further information, contact:



MAYEKAWA MFG. CO., LTD (HEAD OFFICE)
 13-1, Botan 2, Koto-ku, Tokyo, 135, Japan
 Tel: (81-3) 3642 8088 Fax: (81-3) 3643 7094

MAYEKAWA AUSTRALIA PTY. LTD
 Unit 2, 44 McCauley Street Matraville, NSW
 Sydney, Australia.
 Tel: (61-2) 9695 7000 Fax: (62-2) 9695 7001

P.T. MYCOM INDONESIA
 Menara Gracia, 6th Flr., J.L. H.R.
 Rasuna Said Kav. C-17 Jakarta 12940, Indonesia
 Tel: (62-21) 522 0881 Fax: (62-21) 522 0880

MAYEKAWA (M) SDN BHD
 No. 17A, Jalan SS26/6, Taman Mayang Jaya,
 47301 Petaling Jaya, Malaysia.
 Tel: (60-3) 7805 1406 Fax: (60-3) 7805 1409

MAYEKAWA AUSTRALIA PTY LTD
 (NEW ZEALAND BRANCH)
 30 Tui Street Otanuhu Auckland
 P. O. Box 12106, Penrose, Auckland,
 New Zealand
 Tel: (64-9) 276 2305 Fax: (64-9) 276 2306

MYCOM PHILIPPINES CORPORATION
 3rd Floor, MRDC Building, 85 Sen. Gil Puyat Avenue,
 Patanan, Makati City, Philippines.
 Tel: (63-2) 844 0767 Fax: (63-2) 844 0762

MYCOM KOREA CO., LTD
 Palyong Dong 24-20, Changwon Kyungsangnam-Do
 Republic of Korea
 Tel: (82-55) 294 8678 Fax: (82-55) 294 7678

MYCOM INDUSTRY CO., LTD
 No. 836, An Chao Rd, Yen Chao Hsiang,
 Kaohsiung Hsien, Taiwan.
 Tel: (886) 7-616-8073 Fax: (886) 7-616-8063

MYCOM SINGAPORE PTE LTD
 6 Tagore Lane, Singapore 787470.
 Tel: (65) 451 1565 Fax: (65) 451 4932

MYCOM (THAILAND) CO., LTD
 947 Moo 12, 12th Flr., Thosapol Land 3 Bldg.,
 Bangna-Trad Rd, Prakanong, Bangkok 10260, Thailand
 Tel: (66-2) 361 8171 Fax: (66-2) 361 8170

MAYEKAWA MFG CO. LTD
 Ho Chi Minh City Representative Office
 10th Flr., Osic Building, No. 8, Nguyen Hue Blvd, District 1,
 Ho Chi Minh City, Vietnam
 Tel: (84-8) 825 6917 Fax: (84-8) 825 6919