

Bell & Gossett Pump

Mfg: Bell & Gossett

Model: 1X1-1/2X80T

Stock No. DBHK005.

Serial No. 1506649-C98

Bell & Gossett Pump. Model: 1X1-1/2X80T. S/N: 1506649-C98. Unimount 125 motor, 1 hp, 1745 rpm, 230/460 V, 3.6-1.8 FL, 3.7/1.85 SF, 60 Hz, 3 phase. Pump capacity: 5 gpm at 50 ft. head. Maximum rpm: 1800. Inlets: 1-1/2 in. Outlets: 1 in. Overall dimensions: 17-1/2 in. L x 9-1/2 in. W x 15 in. H.

