

## Bell & Gossett Frame Mounted Pump

Mfg: Bell & Gossett

Model: HSC3-10.500-LHR-CN6279

Stock No. DCCT003.

Serial No. 2308635

Bell & Gossett Frame Mounted Pump. Model: HSC3-10.500-LHR-CN6279. S/N: 2308635. Size: 4x6x12L. Capacity: 700 gpm @ 100 TDH. Maximum input hp: 85. Maximum input rpm: 1775. Self-flushing mechanical seals for maximum lubrication, debris removal and heat dissipation. The internally flushed seals allow for a shorter shaft for reduced deflection for longer seal life. General Electric Motor, 25 hp, 1760 rpm, 230/460 V, 60/30 amps. Inlets: (1) 6 in. flanged port. Outlets: (1) 4 in. flanged port. Overall dimensions: 54 in. L x 32 in. W x 31 in. H.



