

Cherry Burrell Votator Scraped Surface Heat Exchanger- 6 x 72

Mfg: Cherry Burrell

Model:

Stock No. DFPC411.21a

Serial No.

Cherry-Burrell Votator Scraped Surface Heat Exchanger- 6 x 72. Model: 655HE. S/N: 89244HA. Contact surface area: 9 ft. sq. Shell MAWP: 400 PSI @ 375 °F. Shell MDMT: -20 °F @ 400 PSI. Jacket MAWP: 150 PSI @ 375 °F. Jacket MDMT: -20 °F @ 150 PSI. Motor, 20 hp, 1155 rpm, 405 rpm (final), 230/460 V, 52/26 amps, 60 Hz, 3 phase. Typical applications are heating and cooling cheese sauce, pudding, caramel, deboned meat, pet food, and fruit products. Inlets: (1) 1-1/2 in. dia. for ammonia, (2) 1-1/2 in dia. threaded fitting (male). Outlets: 2-1/2 in. dia for ammonia, (2) 1-1/2 in dia. threaded fitting (male). Overall dimensions: 9 ft. L x 48-1/2 in. W x 59-1/2 in. H.





