

Alfa Laval Contherm Scraped Surface Heat Exchanger

Mfg: Alfa Laval

Model: 6 x 9

Stock No. DFPC469.67

Serial No. HC6273NPC

Alfa Laval Contherm Scraped Surface Heat Exchanger. Model: 6 x 9. S/N: HC6273NPC. Product side MAWP: 300 PSI @ 300 °F. Media side MAWP: 250 PSI @ 300 °F. MDMT: -30 °F @ 100 PSI. Concentric shafts with (6) 24 in. L x 1-1/2 in. W scrapers. (2) Lincoln A.C. Motors, 7-1/2 hp, 1165 rpm, 376 rpm (final), 230/460 V, 22/11 amps, 60 Hz, 3 phase. Inlets: (2) 2 in. dia. I-line fittings. Outlet: (2) 2 in. S-line for ammonia. Overall dimensions: 88 in. L x 60 in. W x 68 in. H.





