

1999 Dunham-Bush Air-Cooled Liquid Chiller- 420 Nominal Tons

Mfg: Dunham-Bush

Model: ACDX420B

Stock No. DPLS225.43a

Serial No. 12329701B99G

1999 Dunham-Bush Air-Cooled Liquid Chiller- 420 Nominal Tons. Model: ACDX420B. S/N: 12329701B99G. Order: 123297-1. For outdoor use only. Refrigerant: R-22. Test pressure hi/lo: 400/250 psig. Power supply: 460 V, 60 Hz, 3 phase. Control supply: 115 V, 60 Hz, single phase. (2) Dunham-Bush Scroll Compressors, Model: 1215NHF6X6K0EMBJ0C, S/N's: BDC-A0594-03 and BDC-A0595-03, refrigerant: R-22, design pressure hi/lo: 410/250 psig, power supply: 460/400 V, 1330 LRA, 60/50 Hz, 3 phase. (1) Dunham-Bush Scroll Compressors, Model: 1218NHF6X6K0EMBJ0C, S/N: BCC-A0549-03, refrigerant: R-22, power supply: 460/400 V, 1485 LRA, 60/50 Hz, 3 phase. Dunham-Bush Chiller Barrel, Model: FXT24149J09CVR0, S/N: 990511020, Nat'l Bd: 30522, shell side MAWP: 200 psi @ 150 °F, shell side MDMT: -20 °F @ 200 psi, tube side MAWP: 250 psi @ 150 °F, shell side MDMT: -20 °F @ 60 psi. (22) Condenser Fan Motors (ea.), 1.5 hp, 3.0 FLA, 460 V, 60 Hz, 3 phase. Inlets/outlets: (2) 10 in. dia. Victaulic ports. Overall dimensions: 44 ft. L x 90 in. W x 101 in. H.







