

2300 / 4160 V Baldor Electric Motor- 700 HP

Mfg: Baldor

Model:

Stock No. DTTC836B.

Serial No. N041/0288-01060115

2300 / 4160 V Baldor Electric Motor- 700 HP. S/N: N041/0288-01060115. Motor specifications: 3575 rpm, 2300/4160 V, 152/84 amps, 60 Hz, 3 phase. Continuous duty. Type: WP11. Insulation class: F. Overall dimensions: 5 ft. L x 3 ft. 10-1/2 in. W x 4 ft. 3-1/2 in. H.

