

Reliance Electric Motor - 1000 HP

Mfg: Reliance

Model:

Stock No.: DTTC844B.

Serial No.:

Reliance Electric Motor - 1000 HP. Motor specifications: 3575 rpm, 2300/4000 V, 215/124 amps, 60 Hz, 3 phase. Continuous duty. Frame: 19EA5810S. Insulation class: F. Overall dimensions: 5 ft. 7 in. L x 5 ft. 2 in. W x 3 ft. 2 in. H.



