

FMC Pulper-Finisher

Mfg: FMC Technologies

Model: 100

Stock No.: 105.EDN482

Serial No.:

FMC Paddle Pulper / Finisher. Model: 100. Stainless steel frame. Paddle dimensions: (4) 33 ½ in. L x 2 ½ in. Includes: Control panel. General Electric transformer. Type QB. 0.250 KVA, 60 Hz, single phase. Allen Bradley line terminal guard. Catalog No. 1494V-DS60. S/N: A. 600 VAC-250 VDC MAX, 600 amp. Westinghouse Series C motor circuit protector. Catalog No. HMCPD70M2C. Style: 663DC87G17. 600 VAC-250 VDC, 70/30 amps, 60 Hz, 3 phase. W. The FMC 100 Pulper / Finisher reduces tomatoes, fruits, and vegetables to a semi-liquid / liquid state. It eliminates pits and separates seeds, skins, and extraneous materials from pureed pulp. Inlet: (1) 3 in. dia. ACME fittings. Outlet: (1) 4 in. dia. ACME fittings. Pulp discharge: 8 ½ in. L x 4 in. W. Overall dimensions: 8 ft. 4 in. L x 3 ft. 1 in. W x 5 ft. 3 in. H.(ACN450).







