

## FMC Stainless Steel Paddle Pulper / Finisher

Mfg: FMC

Model: 100

Stock No. 145.EDN483

Serial No.

FMC Paddle Pulper / Finisher. Model: 100. Material of Construction: 304 Stainless Steel. Inside straight wall dimensions: 35 in. L x 29 in. W x 15 in. H. Paddle dimensions: (4) 32 in. L x 2 ½ in. W. Elektrim Electric Motor, 20 hp 1755 rpm, 230/460 V, 45.4/22.7 amps, 60 Hz, 3 phase. Drive, ratio: 2.50, 702 rpm out (final). Stainless steel frame with floor mounting plates. Casting frame stamps JE-54, 9501, F-8. The FMC 100 Pulper / Finisher reduces tomatoes, fruits, and vegetables to a semi-liquid or liquid state. It eliminates pits from stoned fruit pulp and separates seeds, skins, and extraneous particulate materials from pureed pulp. Inlet: (1) 3 in. dia. ACME fittings. Outlet: (1) 3 in. dia. ACME fittings. Pulp discharge: 8 ½ in. L x 4 in. W. Overall dimensions: 8 ft. 9 in. L x 3 ft. 3 in. W x 5 ft. 5 in. H.







