

FMC Pulper Finisher with Stainless Steel Frame

Mfg: FMC

Model:

Stock No. END9744.

Serial No.:

FMC Pulper/Finisher with Stainless Steel Frame. Inside dimensions: 35 in. L x 14 in. W x 16 in. H. Inlets/outlets: (1) 3 in., (1) 4 in., (1) 4 in. drain. US Electric Motor, ID E409AIZ06Z128R020F, 20.0 hp, 1,750 rpm, 208-230/460 V, 55.9-49.4/24.7 amp, 60 Hz, 3 phase, 256 T, Type CT, SF 1.15. US Electric Series 2000 Motor Drive, Model CBN2501SB32.50U250NM. Bar: 29 in. L. Bottom lid: 17 in. W x 16 in. H with 1 in. holes. Top lid: 36 in. L x 20 in. W x 7 in. H. (2) Closing outer lids: 34 in. L x 10 in. W. (4) Paddles: (4) 4 in. L x 2-1/2 in. W and (4) 33 in. L x 2-1/2 in. W. Overall dimensions: 105 in. L x 34 in. W x 63 in. H.



