

FMC Paddle Pulper/Finisher

Mfg: FMC

Model: 100

Stock No. END9745.

Serial No.

FMC Paddle Pulper/Finisher. Model: 100. Cast iron frame. Shaft dimensions: 2 in. dia. x 5 ft. L. (2) 34-1/2 in. L x 10 in. W hinged side covers, (1) removable top cover. Electric Motor 10 hp, 220/440 V. Integrated drive. Applications include varieties of citrus and non citrus processing to include: juice finishing (pulp separation), oil finishing (separating frit from oil/water emulsion), butter, dressings, and soups. Inlets: (1) 2 in. dia. acme. Outlets: (1) 2-1/2 in. dia (liquid discharge), (1) 8-1/4 in. L x 4 in. W (pulp discharge). Overall dimensions: 8 ft. L x 4 ft. 3 in. W x 6 ft. H.



