

FMC Paddle Pulper / Finisher

Mfg: FMC

Model: 100

Stock No. END9746.

Serial No.

FMC Paddle Pulper / Finisher. Model: 100. Stainless Steel Frame. Paddle dimensions: (4) 33 ½ in. L x 2 ½ in. Control Panel. General Electric Transformer. Type QB. 0.250 KVA, 60 Hz, single phase. Allen Bradley Line terminal guard. Catalog No. 1494V-DS60. S/N: A. 600 VAC-250 VDC MAX, 600 amp. Westinghouse Series C Motor Circuit Protector. Catalog No. HMCPD70M2C. Style: 663DC87G17. 600 VAC-250 VDC, 70 amps, 60 Hz, 3 phase. W. The FMC 100 Pulper / Finisher reduces tomatoes, fruits, and vegetables to a semi-liquid or liquid state. It eliminates pits from stoned fruit pulp and separates seeds, skins, and extraneous particulate materials from pureed pulp. Inlet: (1) 3 in. dia. ACME fittings. Outlet: (1) 4 in. dia. ACME fittings. Pulp discharge: 8 ½ in. L x 4 in. W. Overall dimensions: 8 ft. 4 in. L x 3 ft. 1 in. W x 5 ft. 3 in. H.





