

## Mycom Cimco C5WO4A 4-Cylinder Reciprocating Compressor – 25 HP

Mfg: Mycom Cimco

Model: C5WO4A

Stock No: ENDX719.3a

Serial No: 95691

Mycom Cimco C5WO4A 4-Cylinder Reciprocating Compressor. Model: C5W04A. S/N: 95691. Refrigerant: last used with R-717 (ammonia). Nominal capacity: 29.2 tons at 32.5 bhp with a 95°F condensing temperature and 20°F suction temperature. Displacement: 110 cfm. Max speed: 1,450 rpm. Bore: 3-3/4 in. Stroke: 3 in. Hydrostatic test pressure (hi/lo): 450/300 psig. Air test pressure (hi/lo): 300/180 psig. Water cooled oil heads and oil cooler. U. S. Electrical motor, 25 hp, 1775 rpm, 575 V, 24 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2 in. dia. flanged ports. Overall dimensions 6 ft. 9 in. L x 3 ft. 2 in. W x 4 ft. 2 in. H. (ACN166-BC/M).







