

Perry Industries Rotary Powder Filler

Mfg: Perry Industries

Model: CMR-1

Stock No. FPPE085.1

Serial No. 2900

Perry Industries Rotary Powder Filler. Model: CMR-1. S/N 2900. All stainless steel contact and frame construction. Continuous motion machine set-up for bottles with a maximum height of 12 in. and a diameter of 3-1/2 in. (3) Port filling wheel, (24) position vibratory funnel turret. Capacity: 200 cpm. Electrical requirements: 230V, 15 amps, 60 Hz, 3 phase. Accofil vacuumetric system for highly accurate versatile vacuum/pressure method of placing powders into ridged containers. For high speed filling of powder and granular products. Reliance Electric Filler Motor, 2 hp, 1760 rpm, 230/460 V, 7.4/3.7 amps, 60 Hz, 3 phase. Sterling/Perfection Gear Drive, 60 ratio, 29.33 rpm (final). Inlets: (1) 5-1/2 in. dia. infeed port (product), (1) 5 in. dia. infeed port (product). Outlets: (3) 2-1/2 in. L x 1/2 in. W discharge ports. Overall dimensions: 60 in. L x 48 in. W x 84 in. H. (ACN350) Rotary hammermill with (9) 5-1/2 in. L x 1 in. W cutting blades. (3) Pneumatic drives. Reliance Electric Hammermill Motor, 3/4 hp, 1780 rpm, 230/460 V, 2.92/1.46 amps, 60 Hz, 3 phase. Reeves XV Variable Speed Motor Drive, 11 ratio, 324 rpm (max), 32.4 rpm (min).





