

Evapco PMC-560 Evaporative Condenser - 560 Tons

Mfg: Evapco

Model: PMC-560

Stock No.: HEBH003

Serial No.: A802167L.H.

Evapco Evaporative Condenser. Model: PMC-560. S/N: A802167L.H. Rated capacities: 560 tons using R-22 at 105°F condensing, 40°F suction and 78°F wet bulb and 406 tons using R-717 at 96.3°F condensing, 20°F suction, and 78°F wet bulb. Baldor Electric motor: 7.5 hp, 1765 rpm, 460 V, 9.40 A, 60 Hz, 3 phase. Baldor Electric motor: 20 hp, 1760 rpm, 230/460 V, 48/24 A, 60 Hz, 3 phase. (3) 5 ft. 1 in. dia. fans. Pulleys dia: (2) 5 in. driver, (3) 1 ft. 7 in. driven. (2) 1 ft. 8 in. dia. manway doors. Inlets/outlets: (2) 3 in. ports, (3) 4 in. ports, (1) 8 in. drain. Overall dimensions: 19 ft. 3 in. L x 10 ft. W x 15 ft. 6 in. H.



