

## Cherry-Burrell 8-Head Rotary Filler

Mfg: Cherry-Burrell

Model: G83L

Stock No. 100.IMS.10

Serial No. \_\_\_\_\_

Cherry-Burrell 8-Head Rotary Filler. Model: G83L. Valve diameter: 1 in. Distance between valves: 10-1/2 in. Maximum size container: 6-1/2 in. L x 4-1/2 in. W x 9-1/2 in. H. Adjustable height. Tank capacity: 30 gal. Inlets: (1) 6 in. dia. port, (1) 10 in. L x 7 in. W port. Overall dimensions: 73 in. L x 31 in. W x 63 in. H.



