



Table 13 Engineering Data

ATC Model No.*	R-717 Tons*	Fans		Weights			Refrigerant Operating Charge lbs.***	Coil Volume ft ³	Spray Pump		Remote Pump			Dimensions				
		HP	CFM	Shipping	Operating	Heaviest Section†			HP	GPM	Gallons Req'd**	Conn. Size	Operating Weight	Height H	Upper U	Lower E	Coil A	Length L
2002B	1,421	(4)20	315,600	74,460	102,380	15,940	1,970	268	(4)5	3,200	1,960	(4)12"	86,480	17' 9-3/4"	9' 7-5/8"	8' 2-1/8"	39-1/4"	24' 2"
2082B	1,478	(4)25	336,000	74,660	102,580	15,990	1,970	268	(4)5	3,200	1,960	(4)12"	86,680	17' 9-3/4"	9' 7-5/8"	8' 2-1/8"	39-1/4"	24' 2"
2158B	1,532	(4)25	325,500	83,980	112,640	18,320	2,355	321	(4)5	3,200	1,960	(4)12"	96,740	18' 6-1/4"	10' 4-1/8"	8' 2-1/8"	47-3/4"	24' 2"
2256B	1,602	(4)25	370,200	84,980	117,960	18,190	2,315	315	(4)5	3,600	2,280	(4)12"	99,560	17' 9-3/4"	9' 7-5/8"	8' 2-1/8"	39-1/4"	28' 2"
2324B	1,650	(4)30	389,500	85,260	118,240	18,260	2,315	315	(4)5	3,600	2,280	(4)12"	99,840	17' 9-3/4"	9' 7-5/8"	8' 2-1/8"	39-1/4"	28' 2"
2404B	1,707	(4)30	377,500	97,100	130,940	21,220	2,760	376	(4)5	3,600	2,280	(4)12"	112,540	18' 6-1/4"	10' 4-1/8"	8' 2-1/8"	47-3/4"	28' 2"
2490B	1,768	(4)20	433,700	94,480	135,620	19,600	2,385	325	(4)7-1/2	4,800	2,880	(4)12"	111,680	17' 1-1/4"	8' 11-1/8"	8' 2-1/8"	30-3/4"	36' 2-1/2"
2647B	1,879	(4)25	466,400	94,680	135,820	19,650	2,385	325	(4)7-1/2	4,800	2,880	(4)12"	111,880	17' 1-1/4"	8' 11-1/8"	8' 2-1/8"	30-3/4"	36' 2-1/2"
2765B	1,963	(4)30	496,500	95,120	136,260	19,760	2,385	325	(4)7-1/2	4,800	2,880	(4)12"	112,320	17' 1-1/4"	8' 11-1/8"	8' 2-1/8"	30-3/4"	36' 2-1/2"
2900B	2,059	(4)25	452,600	107,680	149,940	22,900	2,965	404	(4)7-1/2	4,800	2,880	(4)12"	126,000	17' 9-3/4"	9' 7-5/8"	8' 2-1/8"	39-1/4"	36' 2-1/2"