

Mycom 8-Cylinder Reciprocating Compressor-60 HP

Mfg: Mycom

Model: N8A

Stock No: KWBF190.10

Serial No: 11784

Mycom 8-Cylinder Reciprocating Compressor. Model: N8A. S/N: 11784. Refrigerant: last used with ammonia producing 58.4 tons at 65 bhp with a 95°F condensing temperature and a 20°F suction temperature. Displacement: 182 cfm. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Allis Chalmers electric motor, 60 HP, 1770 rpm, 208-220/440 V, 145-145/72.5 amps, 60 Hz, 3 phase. Driver pulley diameter: 10. Driven pulley diameter: 16 in. Pulley ratio: 0.625. Final speed: 1,106 rpm. Inlets: (1) 3-1/2 in. dia. port. Outlets: (1) 3 in. dia. port. Compressor run time: 18,946 hrs. Overall dimensions: 6 ft. 6 in. L x 3 ft. 6 in. W x 4 ft. 4 in. H.(ACN187).





