

Mycom 8-Cylinder Reciprocating Compressor - 60 HP

Mfg: Mycom

Model: 8A

Stock No: KWBF191.10

Serial No: 8A1059

Mycom 8-Cylinder Reciprocating Compressor - 60 HP. Model: 8A. S/N: 8A1059. Refrigerant: last used with ammonia producing 58.4 tons at 65 bhp with a 95°F condensing temperature and a 20°F suction temperature. Displacement: 182 cfm. Leak test pressure: 300 psig. Hydrostatic test pressure: 426 psig. U.S. electrical motor, 60 hp, 1800 rpm, 440 V, 74 amps, 60 Hz, 3 phase. Driver pulley diameter: 10 in. Driven pulley diameter: 16 in. Pulley ratio: 0.625. Final speed: 1,125 rpm. Inlets: (1) 3-1/2 in. dia. port. Outlets: (1) 2-1/2 in. dia. port. Overall dimensions: 6 ft. 6 in. L x 4 ft. 1 in. W x 5 ft. 4 in. H. Compressor runtime: 7,572 hours. (ACN187).



