

1996 Jordan Ammonia Recirculator Package – 70 in. Dia. x 10 ft. L

Mfg: Jordan Equipment Sales

Model: HRC72-13



Stock No: KWBF709.3

Serial No: 96-1792

1996 Jordan Ammonia Recirculator Package. Model: HRC72-13. S/N: 96-1792. Nat'l Bd: 1646. Nominal capacity: 2,350 gallons. Inside straight-wall dimensions: 70 in. dia. x 10 ft. L. Refrigerant: R-717 (Ammonia). MAWP: 250/130 psi @ +200/200°F. MDMT: -20/-45°F @ 250/130 psi. Radius: 2:1 elliptical ends. (2) Buffalo pumps, Capacity: 105 gpm. Size: 66V-3013. Head: 165. Peerless Winsmith pump motor: 10 hp, 1750 rpm, 35.6/17.8 amps, 230/460 V, 60 Hz, 3 phase. 1996 Jordan oil pot: S/N: HOP10-30. MAWP: 300psi @ 200°F. MDMT: 50°F @ 300 psi. Inlets: (1) 12 in. dia. port, (2) 1-1/2 in. dia. port, (3) 1 in. dia. port. Outlets: (1) 12 in. dia. port, (2) 6 in. dia. port, (1) 2 in. dia. port. Overall dimensions: 14 ft. L x 7 ft. W x 12 ft. 6 in. H.







The Following are Pictures of the Unit in its Previous Installation.

