

## FMC 100 Paddle Pulper / Finisher Stainless Steel

Mfg: FMC

Model: 100

Stock No. 125.L63002.8a

Serial No. CC 1673

FMC Paddle Pulper/Finisher. Model: 100. S/N: CC 1673. Stainless steel. (4) paddles, dimensions: 33-3/4 in. L x 2-1/2 in. each. U.S. Syncrogear Electric Motor, 20 hp, 1800 rpm, 220/440 V, 52/26 amps, 60 Hz, 3 phase. Integrated drive, ratio: 2.59, 690 final rpm. Cast iron frame. Inlets: 4 in. dia. S-line fitting (infeed). Outlets: (1) 2-1/2 in. dia. bevel with hex nut (liquid discharge), (1) 10 in. W x 4 in. H pulp discharge. Applications include varieties of citrus and non citrus processing to include: juice finishing (pulp separation), oil finishing (separating frit from oil/water emulsion), butter, dressings, and soups. Overall dimensions: 8 ft. 5 in. L x 3 ft. 7 in. W x 4 ft. 5 in. H.



