

Vertical Paddle Finisher

Mfg:

Model:

Stock No. OI04

Serial No.:

Vertical Paddle Finisher. 316 stainless steel. (1) Hopper: 26 in. dia. (2) Removable paddles: 1 in. W x 22-1/2 in. H. Finisher: 16-mesh screen. Reliance Electric S-2000 Motor: 1.5 hp, 1725 rpm, 208-230/460 V, 5.6-5.6/2.8 amps, 60 Hz, 3 phase. Perfection American Motor Drive: 30 ratio, 57.5 rpm (final). Inlet: 26 in. dia. Outlets: (1) 1-1/2 in. dia. Q-line fitting, (1) 2 in. dia. (side), (1) 3 in. dia. sump with 3/4 in. dia. drain valve. Overall dimensions: 36 in. L x 34 in. W x 53 in. H.

