

Durco Centrifugal Pump

Mfg: Durco/Durion

Model:

Stock No. OIP082.

Serial No. 227569

Durco Centrifugal Pump. S/N: 227569. Size: 1-1/2x1-6/60. Alloy: D4. Capacity: 15 gpm @ 19 tdh. Maximum design pressure: 275 psi @ 100 °F. Reliance Electric Motor, 2 hp, 3450 rpm, 208-230/460 V, 5.6-5.2/2.6 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. port with 125 lb ANSI flange. Outlets: (1) 1 in. dia. port with 125 lb ANSI flange. Overall dimensions: 36 in. L x 12 in. W x 19 in. H.

