

1996 RVS Recirculating Ammonia Tank – 54 in. Dia. x 10 ft. H.

Mfg: RVS

Model:

Stock No: RGMB112

Serial No: 96904

1996 RVS Recirculating Ammonia Tank. S/N: 96904. Nat'l Bd: 9399. Refrigerant: R-717. MAWP: 150 psi @ 300°F. MDMT: -20°F @ 150 psi. Inside straight-wall dimensions: 54 in. dia. x 10 ft. H. Radius: 2:1 elliptical ends. (2) Cornell pumps. Model: 2CB-5-4. (2) Baldor electric motor – 5 hp, 1760 rpm, 13.6/6.8 amps, 230/460 V, 60 Hz, 3 phase. Inlet/Outlets: (2) 6 in. dia. ports, (1) 4 in. dia. ports, (3) 2 ½ in. dia. ports, (3) 1 in. dia. ports. Overall dimensions: 6 ft. 9 in. L x 6 ft. 4 in. W x 18 ft.4 in. H.(BB).





