

1991 Vilter Recirculating Tank – 36 in. Dia. x 10 ft. L

Mfg: Vilter

Model:

Stock No: RGMB119.2

Serial No:

1991 Vilter Recirculating Tank. Approximate capacity: 525 gallons. Refrigerant: R-717 (Ammonia). Inside straight wall dimensions: 36 in. Dia. x 10 ft. L. Radius: 2:1 elliptical ends. (2) Buffalo pumps. S/N: 91430108-002/NA. GPM: 26.9. (1) Motor - 3 hp, 3500 rpm, 230/460 V, 9.1/4.5 amps, 60 Hz, 3 phase. Oil Pot: Nat'l Bd: 42790. S/N: 45564. MAWP: 300 psi @ 650°F. MDMT: -20°F @ 300 psi. Hansen Technologies Variable-Level Panel. Inlets/Outlets: (3) 1 in. dia. port. (3) 1 ½ in. dia. port. (2) 2 in. dia. port. (2) 4 in. dia. port. (1) ¾ in. dia. port. (2) 3 in. dia. port. Overall Dimensions: 13 ft. 5 in. L x 7 ft. W x 10 ft. 5 in. H.









RES

300 PSI AT 650 °F  
 (MAX. ALLOWABLE WORKING PRESSURE)

-20 °F AT 300 PSI  
 (MAX. DESIGN METAL TEMPERATURE)

1995 SERIAL NO. 45564

C-11883

BUFFALO PUMPS, INC.  
 NORFOLK, ONTARIO, N.Y.

MODEL NO. 14100107-002

MOTOR: 3500 RPM, 3 H.P., 2500 VOLT, 9.1/4.5

MAX. PSI: 300

TEMPERATURE: 150 °F

PROTECTOR: NONE

SERIAL: ST25208

SHAFT ASSY: 84010-0000-0

HEAD SEAL MATERIAL: GRAPHITE

DATE: 3/23/04

Buffalo

BUFFALO PUMPS, INC.  
 NORFOLK, ONTARIO, N.Y.

MODEL NO. 14100107-002

MOTOR: 3500 RPM, 3 H.P., 2500 VOLT, 9.1/4.5

MAX. PSI: 300

TEMPERATURE: 150 °F

PROTECTOR: NONE

SERIAL: ST25208

SHAFT ASSY: 84010-0000-0

HEAD SEAL MATERIAL: GRAPHITE

DATE: 3/23/04

Buffalo

BUFFALO PUMPS, INC.  
 NORFOLK, ONTARIO, N.Y.

MODEL NO. 14100107-002

MOTOR: 3500 RPM, 3 H.P., 2500 VOLT, 9.1/4.5

MAX. PSI: 300

TEMPERATURE: 150 °F

PROTECTOR: NONE

SERIAL: ST25208

SHAFT ASSY: 84010-0000-0

HEAD SEAL MATERIAL: GRAPHITE

DATE: 3/23/04

Buffalo

