

Bell & Gossett Circulating Centrifugal Pump - 3 HP

Mfg: Bell & Gossett

Model: 1-1/2x2x8QT

Stock No: RGMB161.a

Serial No: 1506128

Bell & Gossett Circulating Centrifugal Pump - 3 HP. Model: 1-1/2x2x8QT. SN: 1506128. Capacity: 100 gpm. Max. working pressure: 175 psi. Baldor super-e motor-3 hp, 1760 rpm, 230/460 V, 8.2/4.1 amps, 60 Hz, 3 phase. Inlet: 2 in. suction. Outlet: 1 1/2 in. discharge. Overall dimensions: 3 ft. 10 in. L x 1 ft. 6 in. W x 4 ft. 5 in H.





