

## Bell & Gossett Centrifugal Circulating Pump-3hp

Mfg: Bell & Gossett

Model: 1-1/2x2x8QT

Stock No: RGMB162.a

Serial No: 1506129

Bell & Gossett Circulating Centrifugal Pump-3hp. Model: 1-1/2x2x8QT. SN: 1506129. Capacity: 100 gpm. Max. working pressure: 175 psi. Motor. Baldor super-e motor. 3 hp, 1750 rpm, 230/460 V, 8.4/4.2 amps, 60 Hz, 3 phase. Inlet: 2 in. suction. Outlet: 1-1/2 in. discharge. Overall dimensions: 3 ft. 10 in. L x 1 ft. 6 in. W x 4 ft. 5 in H.







**BELL & GOSSETT**  
**PUMP**  
 GPM: 1000  
 HP: 1.5  
 RPM: 1750  
 MAX. WP: 175 PSI  
**BELL & GOSSETT**  
 100 FORD STREET, LYNN, MASS. 01901



**INCOAN** **TEFC** TOTALLY QUALIFIED REPLACEMENT FOR ODP  
**A.C. MOTOR**  
 HP: 1.5 RPM: 1750 FRAME: 180C  
 VOLTS: 230/480 PHASE: 3 HERTZ: 60  
 AMPS: 8.4/4.2 TIME RATING: CONT.  
 CAN BE USED ON 208V SYSTEM UP TO 9.3 AMPS  
 MAY NOT MEET ALL NEMA PERFORMANCE LIMITS ON 208V SYSTEM  
 SERVICE FACTOR: 1.15 MAX. TEMP: 40 °C  
 INS. NEMA DESIGN: B TEMP. RISE: 80 °C  
 NEMA NOM. EFF: 82.5 NEMA MIN. EFF: 80 INCOAN  
 SERIAL: 4185  
 MADE IN U.S.A.