

**1996 Industrial Service & Fabricators Inc. Ammonia Recirculator - 6 Ft. Dia. x 20 Ft. L**

**Mfg: Industrial Service & Fabricators Inc.**

**Model: HRC 72-257**

**Stock No.: RGMP287**

**Serial No.: 96-1637**

1996 Industrial Service & Fabricators Inc. Ammonia Recirculator - 6 Ft. Dia. x 20 Ft. L. Model: HRC 72-257. S/N: 96-1637. Nat'l Bd: 1524. MAWP: 250/125 psi @ 200°F. MDMT: -20/-50°F @ 250/125 psi. Maximum liquid temperature: 287°F. Maximum ambient temperature: 104°F. (2) Buffalo Pumps Inc. Centrifugal Pumps, Model: 118-31-0071-0, S/N's: BB77581 and PY59596, S/O's: 97440656-001 and 96430323-001, Size: 66M-2013, capacity: 90 gpm @ 120 tdh. (2) Peerless Winsmith Inc. Motors, 5 hp, 1750 rpm, 230/460 V, 92.1/46 amps, 60 Hz, 3 phase. 1996 Industrial Service & Fabricators Inc. Separator- 8 Gallon, S/N: 96-1643, inside straight-wall dimensions: 10 in. dia. x 2 ft. L, MAWP: 300 psi @ 200°F, MDMT: -50°F W @ 300 psi. Hoffman Control Panel, Cat No: A-20H1606SSLP. (2) Square-D Safety Switches. Inlets: (1) 8 in. dia. port, (1) 2 in. dia. port. Outlets: (1) 8 in. dia. port, (1) 2-1/2 in. dia. port, (2) 1-1/2 in. dia. relief ports. Overall dimensions: 21 ft. 4 in. L x 9 ft. 3 in. W x 11 ft. 11 in. H.















