

Mycom 6-Cylinder Reciprocating Compressor – 50 HP

Mfg: Mycom

Model: 6J2

Stock No.: RPCN202a.2a

Serial No.: 11759

Mycom 6-Cylinder Reciprocating Compressor. Model: 6J2. S/N: 11759. Refrigerant: This unit is set up for Freon, R-12, R-22, R-404, and R-502. 50 hp electric motor. Displacement: 165 cfm. Capabilities of the 6J compressor: 74.9 TR at 72.9 BHP with R-22 with a 40°F Suction, 105°F Discharge, 15°F Superheat, and 0°F Subcooling at a max rpm of 1450. Displacement: 165 cfm. Howe recirculator. Connections: 3 in. suction and 2-1/2 in. discharge.(ACN182a-BC/Motor).

