

Groen Stainless Steel Jacketed Kettle-80 Gallon

Mfg: Groen

Model: RA-80

Stock No. SGM4124.32a

Serial No. 117327

Groen Stainless Steel Jacketed Kettle-80 Gallon. Model: RA-80. S/N: 117327. Natd Bd. No. 117327. Kettle inside dimensions: 34 in. dia. x 27 in. H. MAWP: 100 psi @ 338°F. Maximum number of scrapers: 18. Scraper dimensions: 3-1/2 in. L x 1-1/2 in. W. Blade dimensions: 13-1/2 in. L x 5 in. W. Baffle dimensions: 20 in. L x 8 in. W. Howell Electric Motor, 1 hp, 1725 rpm, 208-230/460 V, 4.2 4.2/2.0 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. bevel seat, (1) 2 in. dia. I-line fitting, (1) 1 in. dia. FNPT fitting (steam in). Outlets: (1) 2-1/2 in. dia. to 1 in. dia. S-line valve fitting, (1) 1 in. dia. FNPT fitting (condensate out). Overall dimensions: 4 ft. 3 in. L x 3 ft. 1 in. W x 7 ft. H.





