

## 1990 Viking Rotary Pump

**Mfg: Viking**

**Model: AK125**

**Stock No. SPGP002.2**

**Serial No. 10087278**

1990 Viking Rotary Pump. Model: AK125. S/N: 10087278. Pump is constructed throughout for tough pumping jobs. This pump features positive-lock thrust control for exact rotor and shaft positioning, revolving casing permits selection of port arrangements at 45 or 90 degree angle from that shown. Pump final rpm: 505. Capacity: 22 gpm. Elektrim Motor, 5 hp, 1720 rpm, 230/460 V, 13.0/6.5 amps, 3 phase, 60 Hz. Blackmer Motor Drive, 3.40 ratio. Inlet/outlet: (2) 2 in. dia. NPT (male). Overall dimensions: 53 in. L x 15 in. W x 17 in. H.

