

APV Crepaco 5 Cylinder Homogenizer

Mfg: APV Crepaco

Model: 5DD775

Stock No: TACJ0307A.40

Serial No: 3054

APV Crepaco 5 Cylinder Homogenizer. Model: 5DD775. Serial no: 3054. Rated capacity: 2,430 GPH at 1,600 PSI with (5) 1-3/4 in. dia. plungers. Pulley dia: 11-3/8 in. driver, 3 ft. 8 in. driven. Maximum PSI: 2500. Lincoln motor: S/N: 1466996, 125 HP, 1185 RPM, 460 V, 154 A, 60 Hz, 3 Phase. Dayton motor: Model: 9ZN53. 1 HP, 1725/1425 RPM, 230/460 V, 3.6/4.0//1.8/2.0 A, 60/50 Hz, 3 Phase. Inlets/outlets: (2) 3 in. S-line. (1) 1 in. port. Overall dimensions: 7 ft. 1 in. L x 4 ft. 10-1/2 in. W x 6 ft. 9-1/2 in. H.









