

Indiana Canning Company Paddle Finisher/Pulper

Mfg: Indiana Canning Company

Model: 140

Stock No: TAFM303.6

Serial No: 1415

Indiana Canning Company Paddle Finisher/Pulper. Model: 140. S/N: 1415. Cylindrical chamber: 2 ft. dia. x 2 ft. L. Number of paddles: 4. Paddle dimensions: 1 ft. 11 in. L x 3-1/2 in. W. US electric motor, 15 hp, 1770 rpm, 208-230/460 V, 40.0-37.0/18.5 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. S-line fitting. Outlets: (1) 3 in. dia. S-line fitting, (1) 10 in. L x 3 in. W. (pulp discharge). Overall dimensions: 5 ft. 8 in. L x 3 ft. 3 in. W x 4 ft. H.











MODEL	T791A	FR	254T	ENCL	TE	TYPE	FUT	PH	3
DRGT	6309-2Z-J/C3	INS	6207-2Z-J/C3	INS	40 °C	DUTY CONT.			
ID#	A0EA176R408F	MODEL	F	USABLE ON 200V 60HZ AT 50KAMP/50					
HP	15.0	RPM	1770	CODE	G	DES	B	VOLTS	208-230/460
60 HZ DATA	MINIMUM EFFICIENCY 91.0	MAXIMUM EFFICIENCY 93.5	GUARANTEED EFFICIENCY 89.5	FLA	40.0-37.0/13.5	FLA	46.0-23.0		
	MAX. INRUSH 4.4	NO. OF PH 3	83.5	SP	1.25				
HP	15.0	RPM	1460	CODE	E	DES	A	VOLTS	190/380
50 HZ DATA	MINIMUM EFFICIENCY 88.5	MAXIMUM EFFICIENCY 91.0	GUARANTEED EFFICIENCY 86.5	FLA	45.0/22.5				
	MAX. INRUSH 3.6	NO. OF PH 3	84.0	SP	1.0				

U.S. ELECTRICAL MOTORS
 DIVISION OF EMERSON ELECTRIC CO.
 ST. LOUIS, MO.
 MADE IN U.S.A.

ENERGY EFFICIENT MOTOR
 967738

Y-Δ CONNECTION
 LOW VOLTAGE HIGH VOLTAGE
 Y START Δ RUN Y START Δ RUN