

## Bell & Gossett Centrifugal Pump

Mfg: Bell & Gossett

Model:

Stock No. THHS010.

Serial No. 2113757

Bell & Gossett Centrifugal Pump. S/N: 2113757. Capacity: 624 gpm @ 100 tdh. Maximum speed: 3500 rpm. Impeller diameter: 3 in. Pump construction code: AB. Baldor Super-E Motor, 20 hp, 3525 rpm, 200 V, 52.9 amps, 60 Hz, 3 Phase. Inlets: (1) 3-1/2 in. dia. suction port with an 8-bolt, 9 in. dia. flange. Outlets: (1) 3 in. dia. discharge port with a 4-bolt, 7-1/2 in. dia. flange. Overall Dimension. 46-1/2 in. L x 17 in. W x 22-1/2 in. H.

