

LUX Stainless Steel Vacuum Belt Dryer

Mfg: LUX

Model:

Stock No.: UGHB017

Serial No.:

LUX Stainless Steel Vacuum Belt Dryer. Infeed hopper dimensions: 3 ft. 1 in. W x 3 ft. 10 in. L. Conveyor belt dimensions: 6 ft. 7 in. L x 3 ft. W. (2) Barrel dimensions: 13 in. dia. x 3 ft. L. EG&G Blower, P/N: 6-353042-40. Motor, 10 hp, 3500 rpm, 200-230/460V, 30-26/13 amps, 60 Hz, 3 phase. Sew-Eurodrive Motor, 4 hp, 2025 rpm, 230/460 V, 13.6/4.8 amps, 60 Hz, 3 phase. Sew-Eurodrive Variable Speed Gear Reducer, ratio: 69.84, rpm out: 28. Conveyor infeed height: 3 ft. 7 in. Conveyor exit height: 7 ft. 2 in. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings (washer fluid). Overall dimensions: 13 ft. 8 in. L x 5 ft. 2 in. W x 7 ft. 4 in. H.







