

Cherry Burrell, Vogt Freezer, Model 3D 122, S/N 5789. (3) Sterling 20 hp motor, S/N 79040746, Model B0206FLF1031, 575 volt, 60 hz, 1175 rpm, 22.0 amp. 6 in. pulleys on the motor, (3) 21 in. pulleys. (3) accumulator tanks, maximum working pressure is 200 psi, maximum temperature 400 °F. S/N (1) CR19616, (2) CR19604, (3) CR19017, MPO 1979, P.P.No. 8351099. (3) Sterling Speed troll. Barrel dimensions 76 in. L x 16 in. W x 16 in. H. 1-1/2 in. inlet, (2) 3 in. and 3 in. outlets on each barrel. It has an electrical control panel. The electricity requirements are 575 volt, (3) pumps with 2 in. inlet and 1-1/2 in. outlet each. Overall dimensions of VOGT Freezer are 128 in. L x 69 in. W x 88 in. H.



