

Langsenkamp Stainless Steel Pulper/Finisher

Mfg: Langsenkamp

Model: 68

Stock No. 120.USF-710.10

Serial No. A190

Langsenkamp Pulper/Finisher. Model: 68, S/N: A190. Stainless steel. Cylindrical screen chamber: 21 in. dia x 26 in. L. Tyler mesh size: 9. (4) paddles. Product intake: 19-1/2 in. L x 13-1/2 in. W. Liquid outlet: 2 in. Pomace outlet: 10-1/2 in. L x 3 in. H. US Electrical Motor: 20 hp, 220/440 V, 52/26 amps, 50 Hz/1500 rpm, 60 Hz /1800 rpm, 3 phase. Final speed: 500-600 rpm depending on frequency. Pulpers are designed for the separation of liquids and solids by means of paddles rotating concentrically within a cylindrical screen. The liquid and desired amount of solids pass through the screen. Overall dimensions: 69 in. L x 34 in. W x 55 in. H.



