

FMC Juice Extractor/Finisher

Mfg: FMC

Model: 75 B

Stock No. tPPMI201.

Serial No. CP-829

FMC Juice Extractor/Finisher. Model: 75B. S/N: CP-829. Capacity is between 75-100 gpm. Feed screw diameter: 14 in. New pneumatics. Screen size: 0.020 in. Construction: mild steel frame with stainless steel contact parts. Ideal for finishing fresh fruit products. These machines are sanitary, high-capacity, screw or worm-type machines designed to separate juice from pulp, seed and skins. Last used on Soya to extract the milk. Baldor Super-E Motor, 15 hp, 1765 rpm, 353 rpm (final), 230/460 V, 18.5 amps, 60 Hz, 3 phase. Inlets: 19-1/2 in. L x 7-1/2 in. W infeed. Outlet: 3 in. dia. Tri clamp. Overall dimensions: 90 in. L x 48 in. W x 50-1/2 in. H.





