

Cherry Burrell 304 Stainless Steel Jacketed Processor- 1,000 Gallon

Mfg: Cherry Burrell

Model: FPDA

Stock No: 120.105

Serial No: 1000-66-1382

Cherry Burrell Jacketed Processor- 1,000 Gallon. Model: EPDA. S/N: 1000-66-1382. 304 Stainless steel construction. Top manway cover with 2-1/2 in. flange outlet. Sanitary inside. Flat bottom. Tank inlets/outlets: 3 in. triclamp connection with triclamp 3 in. valve (side), (2) 1 in. threaded (side bottom), (1) 1-1/2 in. (side bottom), (1) 3 in. triclamp (top), (1) 2 in. threaded (top), and (1) 3 in. top vent. Jacket inlets/outlets: (2) 2-1/2 in. Mixer; no spray balls. Motor: 1.5 hp, 230 V, 3 phase, 60 Hz. No Ntl. Bd. Tag. Tank dimensions: 77 in dia x 7 ft H. Mounted on 12 in. legs.





