

Cherry Burrell Pasilac Therm Plate Heat Exchanger

Mfg: Cherry Burrell

Model: N35TKS

Stock No. 186

Serial No. 1085

Cherry Burrell Pasilac Therm Plate Heat Exchanger. Model: N35TKS. S/N: 1085. Test pressure: 85 psi. Max. diff. pressure: 85 psi. Max working temp: 221 F. Inlets/outlets: (4) 3 in. s-line on header, (4) 3 in. s-line on floater. (2) Dividers: 1st divider has (1) 2 in. s-line outlet; 2nd divider has (2) 2 in. s-line outlets. Overall dimensions: 112 in. L x 34 in. W x 85 in. H.

