

Urschel Slicer

Mfg: Urschel

Model: HS

Stock No.: AARF013.36

Serial No.: 672

Urschel Slicer. Model: HS. S/N: 672. Model HS is a centrifugal-type slicer that produces flat slices from 1/16 in. (1.5 mm) to 3/4 in. (19.5 mm) thick. Capacity is determined by the slice thickness and type of product. For example, root vegetables with yield 3,000 lbs/hr (approx.) for each 1/16 in. of slice thickness, 12,000 lbs/hr (approx.) for 1/4 in. cuts, and 24,000 lbs/hr (approx.) for 1/2 in. slices. Slice thickness is adjusted by rotating the knurled adjustment knob. Unit is constructed of both Stainless Steel and Food-Grade Manganese Aluminum Bronze, which is commonly used in vegetable size reduction applications. Electric Apparatus Motor, 2 hp, 1755/1460 rpm, 200/208/230/460 V, 5.8-7/5.5-6.8/5.2-6.2/2.6-3.1 amps, 60/50 Hz, 3 phase. Inlets: (1) 19-1/2 in. L x 15-1/2 in. W infeed hopper. Outlets: (1) 7 in. L x 5-3/4 in. W discharge chute. Overall dimensions: 61 in. L x 40 in. W x 50 in. H. (ACN250-87).



