

1996 Pollution Control Products, Inc. IGG Series Controlled Pyrolysis® Cleaning Furnace

Mfg: Pollution Control Products, Inc.

Model: IGG94

Stock No: ABCC04

Serial No: 4064

1996 Pollution Control Products, Inc. IGG Series Controlled Pyrolysis® Cleaning Furnace. Model: IGG94. Serial No: 4064. Furnace compartment capability: 94 sq. ft. at 350K BTU. Includes Honeywell controls and Truline chart recorder and (2) Midco International Incinomite gas burners, model J82DS. Respective maximum and minimum input ranges: 290K -100K BTU/Hr. The IGG series cleaning furnace uses natural gas at temperatures reaching 900°F to burn off (pollution free) polymers, adhesives and chemicals from screws, dies, breaker plates and other metal tools. Uses natural gas running at 900°F. Overall dimensions: 9 ft. 11 in. L x 5 ft. 7 in. W x 5 ft. 8 in. H.







