

## York 8-Cylinder Reciprocating Compressor

Mfg: York

Model: JS73D3A-S46-50S

Stock No. ACEU1005

Serial No. NM116985

York 8-Cylinder Reciprocating Compressor. Model: JS73D3A-S46-50S. S/N: NM116985. Date code: RT46, power supply: 460 V, 835 LRA, 168 RLA, 60 Hz, 2 phase. Unit control power: 115 V, 60 Hz, single phase. Inlets: (1) 3 in. dia. copper suction tube. Outlets: (1) 2 in. dia. copper discharge tube. Overall dimensions: 97 in. L x 33-1/2 in. W x 44-1/2 in. H.







