

Recold MW-Series Closed Circuit Fluid Cooler- 18 Tons

Mfg: Recold

Model: MWL-18B

Stock No: ASCS245.35a

Serial No: 01708

Recold MW-Series Closed Circuit Fluid Cooler- 18 Tons. Model: MWL-18B. S/N: 01708. Capacity min/max: 25-100 gpm. Coil volume: 42 gal. Airflow: 12,300 cfm. 3 ft. fan. Leeson motor, 5 hp, 1750 rpm, 208-230/460 V, 13.8-13/6.5 amps, 60 Hz, 3 phase. The MW-series is an induced draft, counter flow design fluid cooler. Recold Centrifugal Pump, impeller diameter: 3.38 in., (2) 1-1/2 in. female npt fittings. Motor, 1 hp, 3500 rpm, 208-230/460v, 60 Hz, 3 phase. 2 ft. 2 in., (1) L x 1 ft. 7 in. W access door. Inlets: (1) 3 in. dia. copper tubing (media). Outlets: (1) 3 in. dia. copper tubing (media), (1) 2 1/2 in. dia. FNPT port (drain), (1) 2 1/2 in. dia. FNPT port (overflow). (1) 1/2 in. pipe (makeup connection), (1) 1 in. dia. port (water). Overall dimensions: 5 ft. 2 in. L x 4 ft. 2 in. W x 9 ft. 2 in. H.(ACN205).(BE).





RECOLD

560 W. MERCURY LANE
BREA, CALIFORNIA 92821
TELEPHONE (714) 529-6080

MODEL WW-100 SERIAL NO. 31505

RECOLD LUBRICATION INSTRUCTIONS

BELOW 32° F DUTY	ABOVE 32° F DUTY
ESSO EXXON BEACON 325	MOBIL MOBILUX EP2 SHELL ALVANIA EP2 TEXACO RB2

(1) GREASE FREQUENCY DICTATED BY OPERATING

LEESON

3002100 TEFC D02E

1750 60 208-230 460

5 CONT. 13.8 13 6.5

84T 1.15 16 14.8 7.4

40 B J 3

F4 87.5 82.0

6246 6205

LEESON MOTOR COMPANY

3018K216 0190293 J46

MOTORPUMP 31 STAINLESS FITTED

1.5 X 1.5 VIT ON SEAL

3.38 IHP DIAMETER

1 HP ODP 3500 RPM

3/60/208-230/460V

RCD4390A

RECOLD BREA, CA